

# Open and close your multi-bag filter housing in 30 seconds or less

- Fast**
- Simple**
- Efficient**
- Economical**
- Safe**
- User-friendly**
- Durable**
- Low Maintenance**
- Cost-effective**
- High Productivity**

The revolutionary QIC-LOCK opening mechanism is the answer to users' demands who work in an environment where productivity and safety are the key priorities.

- QIC-LOCK opening mechanism is safe to use. An interlock prevents opening until the housing is entirely vented.
- QIC-LOCK opening mechanism is simple and fast to operate. Standing in place, the operator can rotate the hand wheel and open the cover. There is no requirement to have full movement and access around the housing or use any tools as with conventional bolted closures.
- QIC-LOCK opening mechanism has a rugged design, precision machining assures long life and repeatable operation. A special coating protects the spindle surface from wear and corrosion. The design is approved for all pressure housing design codes.
- QIC-LOCK opening mechanism doesn't just make life easier for operators; there are significant cost benefits to be realized with greatly reduced downtime and lower maintenance costs.



1. Filter element change necessary – open the safety interlock to ensure simultaneous pressure relief.



2. Rotate the spindle using the hand wheel to open the V-clamp into the end position.



3. Open the cover aided by spring-assisted mechanism.



4. Change filter element.



5. Close the cover.



6. Close the V-clamp by rotation of the spindle.



7. Close the safety interlock and the housing is ready to go back on-line.

**North America**  
44 Apple Street  
Tinton Falls, NJ 07724  
Toll Free: 800 656-3344  
(North America only)  
Tel: +1 732 212-4700

**Europe/Africa/Middle East**  
Auf der Heide 2  
53947 Nettersheim, Germany  
Tel: +49 2486 809-0

**Internormen** Product Line  
Friedensstraße 41  
68804 Altlußheim, Germany  
Tel: +49 6205 2094-0

**Begerow** Product Line  
An den Nahwiesen 24  
55450 Langenlonsheim, Germany  
Tel: +49 6704 204-0

**China**  
No. 3, Lane 280,  
Linhong Road  
Changning District, 200335  
Shanghai, P.R. China  
Tel: +86 21 5200-0099

**Singapore**  
4 Loyang Lane #04-01/02  
Singapore 508914  
Tel: +65 6825-1668

**Brazil**  
Av. Julia Gaioli, 474 – Bonsucesso  
07251-500 – Guarulhos, Brazil  
Tel: +55 11 2465-8822

For more information, please email us at [filtration@eaton.com](mailto:filtration@eaton.com) or visit [www.eaton.com/filtration](http://www.eaton.com/filtration)

© 2014 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

US  
EF-FBH-02  
10-2014